

OPPILab Teach Basic

Transparent walls make it easy to follow the teacher's demonstration


- A lightweight fume cupboard equipped with castors can be moved easily to wherever it is needed.
- All walls are made of transparent polycarbonate.
- The fume cupboard is equipped with LED lights and sockets for greater usability.
- The base has a laminate shelf and a polypropylene drain basin for storing chemicals during use.
- The fume cupboard has an optimally designed front edge, continuous handle and side profiles to optimize air flow.




Product information

Standard width	900 mm
Worktop depth	600 mm
Total depth	645 mm
Total height	1-part glass opened 2180 mm. With the sash lowered, 1985 mm.

VISU KALUSTE OY

 Eeliksentie 6, 34870 Visuvesi, Finland

 visu@visu.fi

 +358 44 749 4940

 visu.fi



INNOSTAVIA YMPÄRISTÖJÄ
TIETEELLE JA TUTKIMUKSELLE


Worktop material	Acidproof steel.
Materials of sides and back wall	Transparent, clear polycarbonate.
Front wall	Vertical, clear polycarbonate.
Height adjustment	Fixed 900mm.
Under-desk storage	Polypropylene drip basin
Sockets	IP21, 2 pcs as standard, 5m power cord + plug.

Additional technical information


The technical properties depend on the fume hood width.

Standard widths, [mm]	900	
Air volume, [l/s]	125	The sash 300 mm open, 0.5 m/s inflow.
Standard lights, led W (lumen)	10/(1040)	
Ventilation connection, [mm]	160	2m flexible AC exhaust pipe with D160 quick connect couplings.
Castors	D100	Two fixed, and two turning and lockable.

VISU KALUSTE OY

 Eeliksentie 6, 34870 Visuvesi, Finland

 visu@visu.fi

 +358 44 749 4940

 visu.fi