

## OPPILab Teach Basic

Transparent walls make it easy to follow the teacher's demonstration


- A lightweight fume cupboard equipped with castors can be moved easily to wherever it is needed.
- All walls are made of transparent polycarbonate.
- The fume cupboard is equipped with LED lights and sockets for greater usability.
- The base has a laminate shelf and a polypropylene drain basin for storing chemicals during use.
- The fume cupboard has an optimally designed front edge, continuous handle and side profiles to optimize air flow.




### Product information

<b>Standard width</b>	900 mm
<b>Worktop depth</b>	600 mm
<b>Total depth</b>	645 mm
<b>Total height</b>	1-part glass opened 2180 mm. With the sash lowered, 1985 mm.

### VISU KALUSTE OY

 Eeliksentie 6, 34870 Visuvesi, Finland

 [visu@visu.fi](mailto:visu@visu.fi)

 +358 44 749 4940

 [visu.fi](http://visu.fi)



INNOSTAVIA YMPÄRISTÖJÄ  
TIETEELLE JA TUTKIMUKSELLE


<b>Worktop material</b>	Acidproof steel.
<b>Materials of sides and back wall</b>	Transparent, clear polycarbonate.
<b>Front wall</b>	Vertical, clear polycarbonate.
<b>Height adjustment</b>	Fixed 900mm.
<b>Under-desk storage</b>	Polypropylene drip basin
<b>Sockets</b>	IP21, 2 pcs as standard, 5m power cord + plug.

### Additional technical information


The technical properties depend on the fume hood width.

<b>Standard widths, [mm]</b>	900	
<b>Air volume, [l/s]</b>	125	The sash 300 mm open, 0.5 m/s inflow.
<b>Standard lights, led W (lumen)</b>	10/(1040)	
<b>Ventilation connection, [mm]</b>	160	2m flexible AC exhaust pipe with D160 quick connect couplings.
<b>Castors</b>	D100	Two fixed, and two turning and lockable.

### VISU KALUSTE OY

 Eeliksentie 6, 34870 Visuvesi, Finland

 visu@visu.fi

 +358 44 749 4940

 visu.fi